

Part Number: 5611002080F

General Description	
Color	Blue
Series	561
Configuration	5 mm Lens
Description	5 mm Stand - Off 0.800" WC Blue
Package Options	Bulk Packaging
Sizes	5mm
Lamp Type	Single Color
Viewing	Top View
Polarity	Cathode Right
Lens Style	Non - Diffused

Absolute Maximum Ratings (Ta = 25Â°)	
Derating	from 40Â° @ .5 mA/Â°C
Solder Temperature	260Â° for 5 sec
Operating Temperature	-30 to +85
Storage Temperature	-40 to +100

Operating Characteristics	
Color	Blue
LED Type	High Efficiency
Luminous Intensity Min	0.9
Luminous Intensity Typical	1.5
Test Current mA	20mA
Emitted Color	Blue
Power Dissipation Max	120mW



5611002080F

check stock



[This is a RoHS Compliant Product](#)
[To learn more click here](#)