

European Region

[Download Instructions](#) (multilingual)

FAST

- Charges NiMH batteries in about one hour



EASY TO USE

- LEDs indicating charging status
- Worldwide voltage: 100-240V AC 50/60 Hz




VERSATILE

- Charges 1-4 "AA" or "AAA" NiMH rechargeable batteries at a time



One Hour Battery Charger



Before Using Your Charger:

Please read all instructions and cautionary markings on the battery charger, batteries, and device.

Product Detail:

Designation: 1 Hour Charger

Color: Silver

Charging Capability: 1 to 4 "AA" / 1 to 4 "AAA"

Charging Current: "AA" 2500mA

"AAA" 1000mA

Trickle Charge: "AA" 50mA

"AAA" 20mA

Charging Times: (estimated)	Battery (NiMH)	Capacity (mAh)	Estimated (time)
	AA	2000	60 mins
	AA	2450	72 mins
	AA	2650	78 mins
	AAA	900	60 mins
	AAA	1000	72 mins

Shutoff Mechanism: Timer Control

Max Timer Control 80 mins

Charger Input : DC 12-16V; 1.3A

Weight (charger): 119 grams

Dimensions (mm): 124 x 80 x 28 (H x L x W)

Safety Features: Reverse Polarity Protection
Safety Timer to Prevent Over Charge
Primary Battery Detection
Temperature Control
Minus Delta Voltage Control (-dV)

NOTE: Do not attempt to charge non-rechargeable batteries not specified by Energizer

Important Notice

This datasheet contains information specific to products manufactured at the time of its publication.

©Energizer

Contents herein do not constitute a warranty.