


RECOMMENDED  
CABLE STRIPPING DIM'S

| REV. | DATE     | ECR NO. | DESCRIPTION     |
|------|----------|---------|-----------------|
| NC   | 01/04/11 | XXXXXX  | INITIAL RELEASE |



1 .CONTACT PIN TO SOLDER

|    |               |          |         |     |
|----|---------------|----------|---------|-----|
| 14 | HEX NUT       | BRASS    | NICKEL  | 1   |
| 13 | WASHER        | BRASS    | NICKEL  | 1   |
| 12 | GASKET        | SILICONE | RED     | 1   |
| 11 | BRAID CLAMP   | BRASS    | NICKEL  | 1   |
| 10 | RING          | BRASS    | NICKEL  | 1   |
| 9  | INSULATOR     | DELIRIN  | NATURAL | 1   |
| 8  | CONTACT PIN   | BRASS    | GOLD    | 1   |
| 7  | INSULATOR     | DELIRIN  | NATURAL | 1   |
| 6  | WASHER        | BRASS    | NICKEL  | 1   |
| 5  | SPRING        | SK5      | NICKEL  | 1   |
| 4  | RETAINER RING | BRASS    | NICKEL  | 1   |
| 3  | GASKET        | RUBBER   | RED     | 1   |
| 2  | BODY          | BRASS    | NICKEL  | 1   |
| 1  | SHELL         | BRASS    | NICKEL  | 1   |
|    | DESCRIPTION   | MATERIAL | FINISH  | QTY |

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [ ] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.

UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE:  
0.5 - 8mm ± 0.20mm  
8 - 30mm ± 0.40mm  
30 - 120mm ± 0.50mm

UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE:  
.020 - .315 = ± 0.007"  
.315 - 1.180 = ± 0.015"  
1.180 - 4.724 = ± 0.020"

DO NOT SCALE DRAWING

| APPROVALS     | DATE                 |
|---------------|----------------------|
| DRAWN M.ZHANG | 01/04/11             |
| CHECKED       |                      |
| ISSUED        |                      |
| SHEET 1 OF 1  |                      |
| CAD FILE      | C:/CONNEX/112335.DWG |

# Amphenol Connex

PART DESCRIPTION

BNC CLAMP PLUG  
(FOR RG-59/U CABLE)

PART NO.

112335

DWG. NO. 112335.DWG

REV. NC

SIZE A

SCALE NA