


CONFIGURATION	PART NUMBER	LENGTH
POWERBOSSLITE, CABLE ASSEMBLY, MOLDED, FEMALE, STRAIGHT, SINGLE KEY	P28978-MXX	AS REQUESTED

DIMENSIONS



TECHNICAL DATA

TEMPERATURE RANGE:	-20C to +90C
PROTECTION:	IP 67, NEMA 6P
VOLTAGE RATING:	600VAC/600VDC
AMPERAGE:	25A
BODY:	OIL RESISTANT PVC
CONTACTS:	COPPER ALLOY
CONTACT PLATING:	GOLD OVER NICKEL PLATING
CONNECTOR FACE:	PVC BLACK
COUPLING NUT:	MACHINED ALUMINUM, ANODIZED
CABLE ASSEMBLY:	UL TYPE TC 600V 90°C DRY 75°C WET, EXPOSED RUN (ER) OR MTW 600V 90°C OR STOOW 105°C 600V - CSA STOOW 600V FT2
APPROVALS:	UL, c(UL)
STANDARD CONFORMITY:	UL 2237

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[P28978-M0.5](#) [P28978-M1](#) [P28978-M1.5](#) [P28978-M2](#) [P28978-M2.5](#) [P28978-M3](#) [P28978-M4](#) [P28978-M5](#) [P28978-M8](#) [P28978-M10](#) [P28978-M12](#) [P28978-M14](#)