

| PANDUIT<br>PART NUMBER |          | STUD<br>SIZE | DIMENSIONS in. |               |               |                |               |
|------------------------|----------|--------------|----------------|---------------|---------------|----------------|---------------|
|                        |          |              | A $\pm .03$    | W $\pm .01$   | C $\pm .02$   | M $\pm .03$    | H $\pm .01$   |
| PV10-6R                | -L<br>-D | #6           | 1.05<br>(26.7) | .31<br>(7.9)  | .31<br>(7.9)  | .89<br>(22.6)  | .15<br>(3.8)  |
| PV10-8R                | -L<br>-D | #8           | 1.05<br>(26.7) | .31<br>(7.9)  | .31<br>(7.9)  | .89<br>(22.6)  | .17<br>(4.3)  |
| PV10-10R               | -L<br>-D | #10          | 1.05<br>(26.7) | .31<br>(7.9)  | .31<br>(7.9)  | .89<br>(22.6)  | .20<br>(5.1)  |
| PV10-14R               | -L<br>-D | 1/4"         | 1.23<br>(31.2) | .52<br>(13.2) | .38<br>(9.7)  | .97<br>(24.6)  | .27<br>(6.9)  |
| PV10-56R               | -L<br>-D | 5/16"        | 1.23<br>(31.2) | .52<br>(13.2) | .38<br>(9.7)  | .97<br>(24.6)  | .33<br>(8.4)  |
| PV10-38R               | -L<br>-D | 3/8"         | 1.31<br>(33.3) | .58<br>(14.7) | .41<br>(10.4) | 1.02<br>(25.9) | .39<br>(9.9)  |
| PV10-12R               | -L<br>-Q | 1/2"         | 1.46<br>(37.1) | .72<br>(18.3) | .53<br>(13.5) | 1.10<br>(27.9) | .52<br>(13.2) |

## NOTES:

## 1. UL LISTED AND CSA CERTIFIED FOR:

## A. 600V. MAX. BLDG WIRE

(1000 V. MAX IN SIGNS, FIXTURES & LUMINAIRES),  
AND 14-10 AWG SOLID OR STRANDED  
COPPER WIRE, & 221°F (105°C MAX) TEMP RATING  
WITH THE CT-550 INSTALLATION TOOL #12 STR OR SOL  
& #10 STR W/ CT-1550, CT-1551 INSTALLATION TOOLS.

## B. 300 V. MAX BLDG WIRE,

12-10 AWG SOLID OR STRANDED  
COPPER WIRE, & 167°F (75°C) MAX TEMP RATING  
WITH THE CT-100 INSTALLATION TOOLS.

## 2. MATERIAL:

A. STAMPING - .04" (1.0) THK COPPER, TIN PLATED

B. HOUSING - VINYL, YELLOW

3. STRIP LENGTH - 5/16 <sup>+1/32</sup> <sub>-.0</sub>


## 4. PACKAGE QTY:

STD PKG. - Q=25

STD PKG. - L=50

BULK PKG. - D=500

## 5. DIMENSIONS IN BRACKETS ARE IN MILLIMETERS

CERTIFIED  
LR31212LISTED  
587H  
E52164

|     |      |     |     |                                                 |       |      |     |                                                                                                            |                       |               |                       |
|-----|------|-----|-----|-------------------------------------------------|-------|------|-----|------------------------------------------------------------------------------------------------------------|-----------------------|---------------|-----------------------|
| 06  | 8/09 | SRB |     | Added -Q- packaging code to PV10-12R            |       |      |     |  <b>PANDUIT</b> CORP. | TINLEY PARK, ILLINOIS |               |                       |
| 05  | 2/02 | SAC |     | FOR PV10-12R DIM A WAS 1.47 &<br>DIM M WAS 1.11 |       |      |     |                                                                                                            |                       |               |                       |
| 04  | 5/02 | SRB | SKB | CHANGED (DIMS) TO 1 PL DECIMAL                  | 10231 | LA   | TRO |                                                                                                            |                       |               |                       |
| 03  | 4/02 | SRB | SKB | ADDED PV10-12R                                  | 10171 | LA   | TRO | 2PC. VINYL INSULATED,<br>#12-10 BARREL, RINGS                                                              |                       |               |                       |
| REV | DATE | BY  | CHK | DESCRIPTION                                     | ECN # | CUST | PM  | DRAWN BY<br>FES                                                                                            | CHK'D                 | SCALE<br>NONE | DRAWING NO.<br>A41187 |