




Part No.	Cable Type	Capacitance PF/ft.	Nominal Impedance	Cable Color	Cable O. D.
BNC-C-XX	RG58C/U	30.8	50 Ohms	Black	0.195"

MATERIALS:

BNC Body: Brass, Tarnish Resistant Plating, Center Contact: Gold Plated Brass

Dielectric: PTFE

RATINGS:

Operating Voltage: Shield-Earth: 30VAC/60VDC Max.

Inner Conductor/Shield: 500VRMS Max.

Operating Temperature: +80°C (+176°F) Max.

Nominal Impedance: 50 Ohms

ORDERING INFORMATION: Model BNC-C-XX

XX = Cable Length in inches, length tolerance: ± 0.5 "

Standard Lengths: 18", 24", 36", 48", 60", 72", 96", & 600".