

# Product Information



## 3470UOR100P62

EAN 4031582010565


Swivel castor, housing made of pressed steel, bright zinc plated, blue passivated, double ball bearing swivel head, wheel axle with nut, dustguard, plate fitting.

Wheel centre made of Polyamide, roller bearing

### Technical Data

|                        |                |
|------------------------|----------------|
| Wheel diameter         | 100 mm         |
| Width of Tread         | 36 mm          |
| Size of Plate          | 105 x 85 mm    |
| Plate hole centres     | 80/77 x 60 mm  |
| Plate hole             | 9 mm           |
| Offset                 | 41 mm          |
| Swivel Interference    | 182 mm         |
| Overall height         | 128 mm         |
| Temperature            | - 40 / + 80 °C |
| Standard               | EN 12532       |
| Weight                 | 0.796 kg       |
| Swivel Radius          | 91 mm          |
| Hardness of tread      | D 75 Shore     |
| Load capacity          | 200 kg         |
| Load capacity (static) | 400 kg         |

|                      |   |   |   |   |   |
|----------------------|---|---|---|---|---|
| Roll performance     | + | + | + | + | + |
| Movement noise       | + | + | + | + | + |
| Attrition            | + | + | + | + | + |
| Corrosion resistance | + | + | + | + | + |



## 3470UOR100P62

EAN 4031582010565

