




Plastic Timing Pulleys MXL025

(0.080" / 2.032mm pitch)

Moulded Metric

Pilot Bore

in Polycarbonate - Glass Filled



Type A

Type B

Type C

Dimensions

All dimensions in mm.

Bore tolerance +0.025 / -0.00mm.

General tolerances ± 0.25 mm unless otherwise marked.

Temperature range -40°C to +80°C

Stock Number	Type	No. Teeth	Dp mm	De mm	Df mm	Dm mm	Fw mm	L mm	Bore d mm	Pw mm
7784803	A	10	6.45	5.97	11	11	8	17.5	3	11.2
7784812	A	12	7.77	7.26	12	11	8	17.5	3	11.2
7784815	A	14	9.07	8.56	13	11	8	17.5	4	11.2
7784819	A	15	9.7	9.19	14	11	8	17.5	4	11.2
7784828	A	16	10.34	9.83	15	11	8	17.5	4	11.2
7784821	A	18	11.63	11.12	16	13	8	17.5	6	11.2
7784825	A	20	12.93	12.43	17	13	8	17.5	6	11.2
7784834	B	22	14.22	13.72	19	13	8	17.5	6	11.2
7784837	B	24	15.52	15.01	20	13	8	17.5	6	11.2
7784831	B	30	19.4	18.89	24	17	8	17.5	8	11.2
7784840	B	36	23.29	22.78	28	17	8	17.5	8	11.2
7784843	C	40	25.88	25.37	30	17	8	17.5	8	11.2
7784847	C	44	28.45	27.94	33	17	8	17.5	8	11.2
7784856	C	48	31.04	30.53	35	17	8	17.5	8	11.2
7784859	C	60	38.81	38.3	43	17	8	17.5	8	11.2
7784853	C	72	46.56	46.05	51	17	8	17.5	8	11.2
7784862	C	80	51.74	51.23	56	17	8	17.5	8	11.2