

LOC		DIST		REVISIONS					
—		—		P	LTR	DESCRIPTION	DATE	DWN	APVD
					R	REV PER ECO-15-016062	10NOV15	KG	CD

1.

THIS RCPT. IS DESIGNED TO CONFORM TO THE LATEST ISSUE OF MIL-C-24308.
2.

MAX WIRE INSUL TO BE USED WITH THIS RCPT IS .068 DIA.
3.

STAINLESS STEEL RETENTION CLIPS ARE INCLUDED IN INSERTS.
4.

THIS RCPT. WILL ACCEPT SIZE 20 SOCKET CONTACT M39029/63-368 OR ANY TYCO HD-20 SOCKET CONTACT. CONTACTS ORDERED SEPARATELY.
- 5




MFG'S PART NO. MARKED ON CONNECTOR REPRESENTS KIT NUMBER WITH CONTACTS.
- 6

UL/CSA DESIGNATION STAMPED IN THIS AREA, OPTIONAL.
- 7

RESTRICTED ITAR ASSEMBLY.
- 8

CADMIUM PER QQ-P-416.
- 9

BRIGHT TIN PER ASTM-B-545 .000400-.000550 THK OVER COPPER PER AMS2418 .000050 MIN THK.



SUPSD BY 205187-1	205163-5	-	-	-	9	STEEL PER ASTM-A-109	205163-5
	-	-	-	7	-	-	205163-4
	-	-	-	-	-	STEEL PER ASTM-A-109	205163-3
	-	-	-	-	-	BRASS	205163-2
SUPSD BY 206799-2	205557-2	M24308/2-282F	M24308/2-2F	5	8	STEEL PER ASTM-A-109	205163-1
	MFG'S P/N MARKED ON CONNECTOR	MILITARY P/N ON PACKAGE	MILITARY P/N ON CONNECTOR	REMARKS	SHELL FINISH	SHELL MAT'L	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C. THOMAS	12-DEC-87		 TE Connectivity	
		CHK F.C. BALLEW	10-DEC-87			
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD F.C. BALLEW	NAME	
		PRODUCT SPEC		AMPLIMITE RCPT FOR SOCKET CONTACTS		
		APPLICATION SPEC		HI-DENSITY HD-20 CONNECTOR		
				SIZE 2 (15 POS) SERIES 109		
				SIZE		
				CAGE CODE		
MATERIAL		WEIGHT		DRAWING NO		RESTRICTED TO
SEE CALLOUTS		—		A1 00779 C 205163		—
FINISH		CUSTOMER DRAWING		SCALE		—
				4:1		SHEET 1 OF 1
						REV R