


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—

NOTES:

1. MATERIALS
- ACTUATOR: THERMOPLASTIC, UL 94V-0, BLACK
BASE: THERMOPLASTIC, UL 94V-0, BLACK
COVER: THERMOPLASTIC, UL 94V-0, BLACK
TERMINAL: COPPER ALLOY, SILVER PLATE
CONTACT: STAINLESS STEEL, SILVER CLAD
2. COMPLIANCE:
- ALL MATERIALS AND FINISHES SHALL COMPLY WITH EU
DIRECTIVE 2002/95/EC OF 27JAN2003(RoHS)
3. SPECIFICATIONS:
- RATING: 5mA 5V DC
CONTACT RESISTANCE: 500mΩ MAXIMUM(INITIAL)
INSULATION RESISTANCE: 100MΩ MINIMUM AT 250V DC
DIELECTRIC STRENGTH: 250V AC, 1 MINUTE
OPERATING LIFE: 50,000 CYCLES WITH LOAD
TOTAL TRAVEL: 2.0 [.079]
ACTUATION FORCE: 35gf MAXIMUM
OPERATING TEMPERATURE: -20°C TO 70° C
STORAGE TEMPERATURE: -30°C TO 80° C

4. SOLDER CONDITIONS:



THE CONDITION MENTIONED ABOVE IS THE TEMPERATURE ON THE CU FOIL OF THE PCB SURFACE. THERE ARE CASES WHERE THE BOARD'S TEMPERATURE GREATLY DIFFERS FROM THE SWITCH'S SURFACE. DO NOT ALLOW SWITCH'S SURFACE TEMPERATURE TO EXCEED 260°C

MANUAL SOLDERING

SOLDERING TEMPERATURE	MAX.350°C.
CONTINUOUS SOLDERING TIME	MAX. 5 SECONDS.

PRECAUTIONS IN HANDLING

1. CARE SHOULD BE EXERCISED SO THAT FLUX FROM THE UPPER PART OF THE PRINTED CIRCUIT BOARD DOES NOT ADHERE TO THE SWITCH.




JJLV0UG1070NOPPRTR	2331398-2
JJLV0UG1070NOPPRTB	2331398-1
SMART PART NUMBER	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN GANESH C M 03MAY2018	TE TE Connectivity Ltd.			
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK ALEXANDER SHARPE 03MAY2018				
		APVD ALEXANDER SHARPE 03MAY2018	NAME SWITCH, DETECTOR, JJL SERIES, 6.5X3.9mm, VERTICAL, SMT, POSTS, 10.7mm			
	0 PLC ± - 1 PLC ± - 2 PLC ± 0.20 [.008] 3 PLC ± - 4 PLC ± - ANGLES ± -	PRODUCT SPEC —	SIZE A3			
		APPLICATION SPEC —				
MATERIAL —	FINISH —	WEIGHT	CAGE CODE 00779	DRAWING NO C-2331398		RESTRICTED TO —
		CUSTOMER DRAWING		SCALE NTS	SHEET 2 OF 3	REV A





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—

PACKAGING:
2331398-1 : 50 SWITCHES PER TUBE
2331398-2 : 400 SWITCHES PER REEL

THE DIMENSION OF TUBE, CARRIER TAPE, COVER TAPE AND REEL



THE DIRECTION OF PILOT HOLES



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN GANESH C M 03MAY2018	TE Connectivity Ltd.		
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK ALEXANDER SHARPE 03MAY2018			
		APVD ALEXANDER SHARPE 03MAY2018	NAME SWITCH, DETECTOR, JXL SERIES, 6.5X3.9mm, VERTICAL, SMT, POSTS, 10.7mm		
	0 PLC ± — 1 PLC ± — 2 PLC ± 0.20 [.008] 3 PLC ± — 4 PLC ± — ANGLES ± —	PRODUCT SPEC — APPLICATION SPEC —	—		
			SIZE A3	CAGE CODE 00779	RESTRICTED TO —
MATERIAL —	FINISH —	WEIGHT	DRAWING NO C-2331398		
CUSTOMER DRAWING		SCALE NTS	SHEET 3 of 3	REV A	