


FJ-05-D-04.80-2

FJ SERIES

FLAT FLEXIBLE CABLE (FFC) JUMPER

Mates with:
FC1, ZF1


Conductor:
Tin Plated Copper
Conductor Resistance:
300 Ω /km max
Insulation Resistance:
12 M Ω /km min
(conductor-to-conductor)
Dielectric Test:
400 VAC during 1 minute
(conductor-to-conductor)
Temperature Rating:
-30°C to +80°C
Voltage Rating:
300 VAC
Flame Resistance:
VW-1 (UL 758)
RoHS Compliant:
Yes



Variety of pin counts

Variable
lengths

FJ	NO. OF POSITIONS	STYLE	OVERALL LENGTH	STRIP LENGTH
	-05, -10, -15, -20, -25, -30	-D = Double End -R = Reversed End	-“XX.XX” = Specify OVERALL LENGTH in inches ($\pm 1/8$ inch) (-D = (50,80 mm) 2.00" minimum)	-2 = (2,00 mm) .079" -4 = (4,00 mm) .157" (Required for mating with FC1 & ZF1)



STRIP LENGTH	C
-2	(2,00) .079
-4	(4,00) .157

Note: Some sizes, styles and options are non-standard, non-returnable.

-D Style

-R Style