



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AJ	00		M1	REV PER ECO 06-029805	2/6/2007	DW	JL
			M2	REVISED PER ECO-09-020689	02SEP09	KK	AEG



1. USE INSTRUCTION SHEET 9050
- USE HAND TOOL 354940-1
- THIS PART NUMBER IS RESTRICTED, SEE SEPARATE RESTRICTED CUSTOMER DRAWING
- OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

RECOMMENDED STRIP LENGTH

SUPERSEDED	RG-174/U,188/U & 316/U	220210-1	220009-5	30.48 [1.200]	21427-2	9-328666-0	2-221149-0	221455-3	9-228979-1
	RG-59/U,59A/U,59B/U,62/U,62A/U & 62B/U	220189-2	220187-2	30.48 [1.200]	-	9-50428-0	1-221149-3	221455-2	9-228979-0
OBSOLETE	---	-	-	-	-	-	-	-	1-228979-8
OBSOLETE	BELDEN YR40862	220189-1	220187-1	30.48 [1.200]	-	9-50427-1	3-221149-6	221455-1	1-228979-7
SUPERSEDED BY 221199-5	RG-179/U,179A/U,179B/U,187/U & 187A/U	220210-1	220009-5	30.48 [1.200]	21427-2	9-328666-0	3-221149-1	221455-3	1-228979-6
SUPERSEDED BY 228979-6	-	-	-	-	-	-	-	-	1-228979-5
SUPERSEDED BY 228979-5	-	-	-	-	-	-	-	-	1-228979-4
OBSOLETE	BELDEN 9907	220189-1	220187-1	30.48 [1.200]	-	9-50427-1	2-221149-6	221455-5	1-228979-3
OBSOLETE	BELDEN 8281	-	220189-6	38.10 [1.500]	-	9-331256-0	221149-6	221455-4	228979-8
	RG-174/U,188/U & 316/U	220210-1	220009-5	30.48 [1.200]	21427-2	9-328666-0	2-221149-0	221455-3	228979-7
	RG-59/U,59A/U,59B/U,62/U,62A/U & 62B/U	220189-2	220187-2	30.48 [1.200]	-	9-50428-0	1-221149-3	221455-2	228979-6
	RG-58/U,58A/U,58B/U,58C/U,141/U & 141A/U	220189-1	220187-1	30.48 [1.200]	-	9-50427-1	221149-6	221455-1	228979-5
FOR USE WITH CABLE		DIE SET	CRIMP TOOL	A	BUSHING QTY = 1	FERRULE QTY = 1	CONTACT QTY = 1	JACK ASSY QTY = 1	PART NO