


Shape

KSSG2308



Model Number	KSSG2308
Rated Input (W)	0.1
Maximum Input (W)	0.15
Impedance (Ω)	$8 \pm 15\% @ 2\text{KHz} 1.0\text{V}$
Rated Frequency (Hz)	$1500 \pm 20\% @ 1.0\text{V}$
Sound Pressure Level (dB)	$88 \pm 3\text{dB} (0.1\text{W}/10\text{cm}), 77 \pm 3\text{dB} (1\text{W}/1\text{m}) @ 2.0\text{K}, 2.5\text{K}, 3.0\text{K}, 4.0\text{KHz}$
Frequency Range (Hz)	Fo---6K
Magnet (mm)	$\varnothing 6.5 \times 1.5$ Rare
Operating Temperature ($^{\circ}\text{C}$)	-20 ~ +55
Weight (Gram)	3.2
Material	ABS UL-94 1/16" HB

Dimension



Tol : ± 0.3 Unit : mm

Characteristic

