






Modular Jack with PCB Leads

154-7616PCB

KOBI CONN

Modular Jack with PCB Leads

154-7616PCB



Dimensions: In.

PCB Layout

ELECTRICAL SPECIFICATIONS

Current Rating:	1.5A max.
Voltage Rating:	150VAC max.
Dielectric Strength:	1000VAC, RMS, 60Hz, for 1 Minute
Contact Resistance:	20mΩ max., Initial
Insulation Resistance:	500MΩ min.

MATERIALS

Color:	Gray
Contact:	.45mm (.018") Dia., Phosphor Bronze
Plating:	Gold Plating over Nickel
Housing:	Glass Filled Polyester
Finish:	.15μ m/.6μ inch Minimum Gold Over Nickel 1.0um/40u inch min.

MECHANICAL SPECIFICATIONS

Operating Temperature:	-40°C ~ +80°C
Insertion Force:	500gms for 4 Contacts
Retention Strength:	7.7kgs Between Jack and Plug
H2S Gas:	25°C - 86hrs.
Durability:	500 Cycles Meets Contact Resistance Test Check Every 100 Cycles. Mating and Unmating Cycles @ 20 Cycles/Minute.

Date Last Revised: 10-19-05

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC-300607

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[154-7616PCB](#)