


# PCB Modular Jack

154-UL6882

**KOBI CONN**

PCB Modular Jack



Dimensions: mm (in.)

SPECIFICATIONS	
Type:	8P8C modular with PCB leads
Rating:	125V, 1.5A
Dielectric withstand voltage:	1000VAC 60Hz
Contact resistance:	30mΩ max.
Insulation resistance:	500MΩ min.
Insertion force:	900g
Housing:	15% glass filled PBT, Black
Contacts:	0.35mm thickness phosphor bronze, gold plated over nickel on contact area, tin plated over nickel on solder area.
Temperature:	-40~80°C
Durability:	500 cycles min.

Date Last Revised: 6/1/10

Available from Mouser Electronics  
1-800-346-6873 / [www.mouser.com](http://www.mouser.com)

KC-300625

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

154-UL6882

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[154-UL6882](#)