

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0191600002

Status:

Active

Description:

Closed-End Insulated Splice for 10-16 AWG Wire


Documents:

Drawing (PDF)

Product Specification PS-19160-005 (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Splices
Series	19160
Mil-Spec	N/A
Product Name	Closed-End Insulated
Physical	
Barrel Type	Closed
Flammability	94V-0
Insulation	Nylon (PA)
Packaging Type	Bag
Temperature Range - Operating	105°C
Wire Insulation Diameter	9.65mm (.380") max
Wire Size AWG	10
Wire Size AWG	12
Wire Size AWG	14
Wire Size AWG	16
Electrical	
CSA	LR18689
UL	E32244
Voltage - Maximum	600V
Material Info	
Old Part Number	NC-1610
Reference - Drawing Numbers	
Product Specification	PS-19160-005
Sales Drawing	SD-19160-001



MATERIAL: COPPER

Series image - Reference only

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Halogen-Free

Status

Not Reviewed

China RoHS

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
19160 Series

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.
Global

Description	Product #
Hand Crimp Tool	0640010600
Crimp Head for the AT-200™ Pneumatic Hand Tool	0640050600
Crimp Head for the AT-200™ Pneumatic Hand Tool, Crimp from Top	0640053500

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION