



FEATURES:

- Extra long grabber can attach to terminal sizes up to .060" (1,5mm) O.D.
- Grabber fits into panel entry openings as small as .250" (6,35mm) diameter.
- Hook is gold plated beryllium copper for superb strength and low contact resistance.
- Do-It-Yourself feature enables the user to create custom patch cord lengths.
- Stainless steel compression spring resists corrosion and retains a firm feel throughout the life of the grabber.

SIMPLIFIED ASSEMBLY PROCEDURE:

1. Pull off thumb cap to expose contact connection.
2. Thread wire through the thumb cap and strip wire insulation .125" (3,18mm).
3. Insert stripped end through tapered hole on contact and solder.
4. Slide thumb cap back onto the contact.

MATERIALS:

Contact: Beryllium Copper, Gold Plated

Spring: Stainless Steel

Insulation: Nylon 6, Marking: "POMONA ELECTRONIC 4225" or "POMONA ELECTRONIC 4565"

RATINGS:

Operating Voltage: 300 VRMS

Operating Temperature: +102°C (+216°F)

Current: 5 Amperes

ORDERING INFORMATION: Models 4225-*, 4565-*

* = Color, Standard Colors: -0 Black, -2 Red

All dimensions are in inches. Tolerances (except noted): .xx = \pm .02" (.51 mm), .xxx = \pm .005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[4565-2](#) [4225-2](#) [4225-0](#) [4565-0](#)