

PIPE SURFACE THERMOCOUPLE up to 350°C

A type J & K stainless steel pipe clamp sensor with adjustable diameter

- 1 Grounded tip for fast response
- 2 Rated 350°C
- 3 Fits pipe diameters 13mm to 55mm (4 sizes)
- 4 2m glassfibre stainless steel braided extension lead, 7/0.2mm

Dimensions & Codes

	Farnell code	LAB code
Type J, 2m lead 13-20mm	8597960	FP-13/20-J-2M
Type J, 2m lead 20-30mm	8597979	FP-20/30-J-2M
Type J, 2m lead 30-40mm	8597987	FP-30/40-J-2M
Type J, 2m lead 40-55mm	8597995	FP-40/55-J-2M
Type K, 2m lead 13-20mm	8598002	FP-13/20-K-2M
Type K, 2m lead 20-30mm	8598010	FP-20/30-K-2M
Type K, 2m lead 30-40mm	8598029	FP-30/40-K-2M
Type K, 2m lead 40-55mm	8598037	FP-40/55-K-2M



Data Ref: FAR 37