




## Product Data Sheet

Part No. GT-0901A Non-Washable Type

### DIMENSIONS



$\phi 9 \times H4.5$

UNIT : mm  
TOLERANCE :  $\pm 0.3$   
HOUSING MATERIAL : PBT

| Type                                                   | Unit         |                |
|--------------------------------------------------------|--------------|----------------|
| Color                                                  |              | Black          |
| Rated Voltage                                          | (V)          | 1.5            |
| Operating Voltage                                      | (V)          | 1-3            |
| Current Consumption                                    | (mA)         | MAX.80         |
| Coil Resistance                                        | ( $\Omega$ ) | $6.0 \pm 15\%$ |
| Sound Output (Min)                                     | (dB)         | 85(Typ)        |
| Resonance Frequency                                    | (Hz)         | 2730           |
| Operating Temp                                         | (C)          | -20~+60        |
| Storage Temp                                           | (C)          | -40~+80        |
| Weight                                                 | (g)          | 1              |
| Terminal                                               |              | PIN TYPE       |
| Dimension                                              | mm           | 9 x H4.5       |
| *applied voltage: Rated Voltage, 1/2 duty, square wave |              |                |
| *distance for measurement: 10cm                        |              |                |

### FREQUENCY RESPONSE

