

Modular Printing System
Ap800 Series



Modular printing system offering the benefits of desktop, portable or in vehicle uses. Choice of impact or high speed thermal printing technologies, standard RS232C interface.

W = 82 D = 158 H = 104

- Impact or thermal printing
- Powered by NiCad battery, mains power supply or from a vehicle (12V system)
- Sits on a desktop, counter or mounts on a wall or vehicle dashboard
- Uses Epson impact dot matrix or fixed head thermal head print mechanism
- Advanced software control
- Text and graphic printing capability
- Easy maintenance
- Data buffer and print spooling to speed up processing

Specification:	Ap892	Ap863
Order Code	391-6078	391-6080
Printer type	40 column impact	24, 32 or 42 column thermal
Print speed	1.7 lines/sec	10 lines/sec
Weight	640g including 48mm paper roll & battery pack	
Power option 1	Battery pack + charger (UK, Euro & USA versions) + data/charger cable	
Power option 2	AC Mains adapter (110 to 230V input) + data cable + mains lead	
Consumables	Paper roll 177-306 Ink ribbon 308-213 Paper roll 391-6170	

Power Option 4: The AP890 & AP892 require an external dc supply capable of delivering a peak current of 5A. The positive connection should be protected with a 7A fuse.
The AP863 requires the external supply to be capable of delivering a peak current of 10A. The positive connection should be protected with a 10A fuse.

234098

Printer Options	Mftrs. List No.	Order Code	Price Each
40 Col Impact	Ap892	391-6078	
24, 32, or 42 Col Thermal	Ap863	391-6080	
Power Options			
Mains Adapter - Requires input lead		391-8610	
Battery pack (NiCd)		391-6091	
Cables			
OEM Data & power socket.			
2M open ended		391-6145	
9 way D type & power socket. 1.2M		391-6157	
Mains Leads			
UK plug - black -2M		112-4388	
Euro plug - black -2M		841-614	
Consumables			
Black Ink ribbon		440-8172	
Thermal paper roll		391-6170	