




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NUMBER*	MAXIMUM CABLE DIA. in. (mm)	WEIGHT lbs/100 pcs (g)/100 pcs	HOLE SIZE DIA. RANGE	PANEL THK. RANGE
LWC19-H25	0.19 (4.8)	0.33 (150)	3/16"-1/4" (5-6)	0.025-0.105 (0.6-2.7)

NOTES:

- SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.



DIMENSIONS IN BRACKETS ARE METRIC [mm]

CAD FILENAME/LAYERS G03597GI_DC_GB0239EY/00B

PANDUIT

CORP.

TINLEY PARK, ILLINOIS

LWC19-H25
LATCHING WIRE CLIP

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ±0.05 (1.3) (.XXX) ±0.010 (0.25)
(.XX) ±0.02 (0.5) ANGLES ± 5°

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY CGSM

MAT'L:

SCALE 2X

DATE 2/14/97

NYLON 6/6

DRAWING NO.

GB0239EY

DRG
A
SIZE

00B	04-13-09	GDH	DN	UPDATED PANEL THICKNESS RANGE CONVERSION	GB0239EY	00B	KLW
2	2-4-99	CGSM		CHANGED DIM. TO REF. DIM. UPDATED FILE NAME	GB0239EY	2	
1	12-15-97	Jod		.41 DIMENSION WAS .19, .86 DIMENSION WAS .85	GB0239EY	1	
R	2/14/97	CGSM		INITIAL RELEASE	GB0239EY	R	
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST SUP