

Fiber optic coupling - PSM-SET-FSMA-LINK/2 - 2799416

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Coupling; set consisting of 2 couplings for connecting F-SMA plugs



Why buy this product

- ✓ Suitable for fiber types:
- POF (980/1000 µm)
 - PCF (200/230 µm)
 - GOF MM (50/125µm)
 - GOF SM (9/125µm)

RoHS

Key Commercial Data

Packing unit	1 STK
GTIN	 4 017918 118396
GTIN	4017918118396

Technical data

Mechanical characteristics

Connection profile	FSMA
Fiber	POF, PCF, GOF
Connection method	Coupling
Color	Bare metallic
Degree of protection	IP20

Ambient conditions

Ambient temperature (operation)	-25 °C ... 85 °C
Degree of protection	IP20

Material data

Flammability rating according to UL 94	V0
Material	Zinc die-cast
Depth	23.5 mm

Fiber optic coupling - PSM-SET-FSMA-LINK/2 - 2799416

Technical data

Material data

Fiber	POF, PCF, GOF
-------	---------------

Standards and Regulations


Flammability rating according to UL 94	V0
--	----

Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"


Drawings

Drilling diagram



Drilling diagram F-SMA panel feed-through

Dimensional drawing



Dimensional drawing F-SMA coupling

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		EAC-Zulassung
-----	---	---------------

Phoenix Contact 2018 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>