



NEUTRIK

Home

Products

About us

Contact

Support



[Products](#) > [Audio](#) > [XLR](#) > [XLR Chassis Connectors](#) > [D Series](#) > NC3FDM3-H-B

[print](#)

NC3FDM3-H-B

3 pole female receptacle, horizontal PCB mount, black metal housing, gold contacts, M3 mounting holes

Universal D-size metal body XLR panel mount series for pcb mount applications. Insert is removable from shell for ease assembling. UL recognized component.

Features & Benefits

- D-shape metal shell
- Optimal RF protection using 3 shield contacts
- Insert is removable from rear of connector and locked into place by internal latch - permitting assembling and testing of pcb before assembling into housing
- Front or rear panel mount



Downloads

-  [Product Guide 2012, 02 XLR](#)
-  [Drawing NC3FDM3-H](#)
-  [Drawing NC3FDM3-H](#)

Links

-  [UL Certificate \(ECBT2.E135070\)](#)

Technical Information ▾ [hide](#)

Product	
Title	NC3FDM3-H-B
Connection Type	XLR
Gender	female
Electrical	
Capacitance between contacts	≤ 4 pF
Contact resistance	≤ 5 mΩ (inner)
Dielectric strength	1,5 kVdc
Insulation resistance	> 2 GΩ (initial)
Rated current per contact	6 A
Rated voltage	50 V
Mechanical	
Insertion force	≤ 20 N
Withdrawal force	≤ 20 N

Lifetime	> 1000 mating cycles
Wiring	Horizontal PCB mount
Locking device	Latch lock
Mounting direction	rear
Chassis shape	D
Mounting	Mounting holes with M3 threads

Material	
Contact plating	0.2 µm Au hard alloy over 2 µm Ni
Contacts	Bronze (CuSn6)
Insert	Polyamide (PA 6.6 30 % GR)
Locking element	Stahl Ck67
Shell	Zinc diecast (ZnAl4Cu1)
Shell plating	Black chromium

Environmental	
Approvals	UL
Flammability	UL 94 HB
Standard compliance	IEC 61076-2-103
Protection class	IP 40
Solderability	Complies with IEC 68-2-20
Temperature range	-30 °C to +80 °C

Accessories



CAS-DUMMY



DBA-BL



DSS-*



NDF



SCDF



SCDP-*



SCDX



SCF

