


ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

REVISIONS		DOC. NO.	SPC-F005	* Effective:	12/21/98	* DCP No:	880	
DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
615	A	Released	JMM	7/10/00	JC	8/11/00	DJC	8/22/00



**Specifications**

1. Alligator style contact can grasp terminals to Ø12.7 [.50]
  2. IEC61010 Ratings: 1000 V CAT III  
6A
- Reinforced or double insulation
3. Materials: Body - Polyamide (Nylon) & Santoprene  
Tip - Brass, Nickel Plated
  4. Internal Resistance: <50 milliohms
  5. Temperature: -20°C to +80°C



**DISCLAIMER:**  
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL. THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.



UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.		DRAWING TITLE: <b>Alligator Style Flexible Clip - Red</b>	
DRAWN BY:	DATE:	SIZE	DWG. NO.
Jeff McVicker	7/10/00	A	76-062
CHECKED BY:	DATE:	ELECTRONIC FILE	
John Cole	8/11/00	16F7729.dwg	
APPROVED BY:	DATE:	SCALE:	SHEET:
Daniel Carey	8/22/00	NTS	1 OF 1