





Standard Profile Right Angle Jacks



Dimensions				
No. of Positions	A	B	C	D
4	13.72 .540	11.18 .400	7.62 .300	3.81 .150
6	15.75 .620	13.21 .520	10.16 .400	6.35 .250
8	17.78 .700	15.24 .600	11.43 .450	8.89 .350

Materials

- Housing:

Standard Material Glass Filled Polyester UL 94V-0

Standard Color Black
- Contact:

0.35mm (0.014”) Thickness Alloy C210. Gold Plating Over Nickel Over Tin
- Gold Plating:

As Per Customer Request.

Ordering Information

Positions/ Contacts	Description	W/ Flange	Flangeless
4P2C	Standard Profile	303042	303042FL
4P4C	Standard Profile	303044	303044FL
6P2C	Standard Profile	303062	303062FL
6P4C	Standard Profile	303064	303064FL
6P6C	Standard Profile	303066	303066FL
8P8C	Standard Profile	303088	303088FL

Standard contact plating is 15 micro inches of gold. For optional platings add dash number as follows:
-6= 6 Micro inches
-30= 30 Micro inches
-50= 50 Micro inches