



Your Sensor Partner

SECATEC electronic GmbH
Knappenstrasse 154
D-57581 Katzwinkel

phone: +49 2741 9460-0
fax: +49 2741 8501

mail: info@secatec.de
web: www.secatec.de

technical data

31.10.2013

reed-magnetic switch

AC/DC 2-wire

Ø10mm / M12 x 1



ident-no.:
71372_CO
type:
Conrad-Typ: 792837

revision index: 000

output	NO
switching capacity	max. 60 W/VA
switching voltage	230 V AC/DC
switching current	max. 3000 mA
switch on time	2,5 ms
switch off time	0,1 ms
switching frequency	max. 200 Hz
lifetime at nominal load	10 ⁵ to 10 ⁶ operations
operating temperature range	-40°C ... +200°C
degree of protection acc. to DIN 60 529	IP67
dielectric test voltage ac (rms.) Ui	2000 V
on/off indication	- - -
housing material	stainless steel
connection	1m silicone-cable 2 x 0,75mm ²

Applications are inadmissible when safety of persons depends on the function of the device.

SECATEC electronic GmbH reserves the right to change or discontinue these products without notice and does not assume any liability arising by use the product with non-compliance of this specifications.



Schutzvermerk nach DIN 34 beachten			(Zul.Abw.) Allgemeintol. nach DIN ISO 2768-m	Oberfläche nach DIN 3141	Maßstab 1:1 (Werkstoff, Halbzeug) (Rohteil-Nr.) (Modell- oder Gesenk-Nr.)	(Gewicht)
			2013	Datum	Name	
			Bearb.	31.10.	CS	
			Gepr.			
			 Secatec electronic GmbH Knappenstraße 154 D-57581 Katzwinkel (0049)02741/9460-0 www.secatec.de			
						Hochtemp. Magnetschalter ø10x60mm Schließer
						(Zeichnungsnummer) 71372_CO
						Blatt
						Bl.
Änderungsindex	Datum	Name	(Urspr.)			(Ers.f.:)
						(Ers.d.:)