




8928 Series

BNC Right Angle



Material:

Insulator: PE-606.

Center Contact: Copper Alloy, Gold Plated.

Body: Diecast (Zinc #3) Nickel Plated.

Mounting Post: Metal, Tin Plated.


Solder Tail: Copper, Wire, Tin Plated.

Washer: Metal, Nickel Plated.

Nut: Copper Alloy, Nickel Plated.

Features:

- * Available in 50 & 75 ohm version.
- * Bayonet locking.
- * Choice of two profile (A & B).



Recommended Mounting Hole.
Maximum Panel Thickness: 5.5mm.
Recommended Mounting Torque: 12 Inch-Pounds Max.

Type	A	B
Dimension		
X	15.8	12.7
Y	8.2	6.8
Z	3.9	3.6

Ordering information

8928-

Series

A

A: Type A
B: Type B
(Profile)

1

1: With Washer & Nut
Blank: Without Washer & Nut

Z

Z: Zinc Body

-50

50: 50 ohm
75: 75 ohm

A

A: Tray Package