




.XXX = in
XX.X = mm

- NOTES:
1. DESIGNED FOR USE WITH RG 174, 316 CABLES
 2. CAPTURED CENTER CONTACT

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
01 ₂	REVISED	DAC 6/15/99	DCm 6/16/99

HOUSING CAP	STAINLESS STEEL PER ASTM-A484 AND ASTM-A582, TYPE 303	GOLD PLATE PER MIL-G-45204
COUPLING NUT	STAINLESS STEEL PER ASTM-A484 AND ASTM-A582, TYPE 303	PASSIVATE PER ASTM-A380
DIELECTRIC	TFE FLUOROCARBON PER ASTM-D-1457	N/A
CENTER CONTACT	BRASS PER ASTM-B-16 HALF HARD	GOLD PLATE PER MIL-G-45204
RETAINING RING	BERYLLIUM COPPER PER ASTM B 194, ALLOY C17200, CONDITION H	N/A
GASKET	SILICONE RUBBER PER ZZ-R-765	N/A
FERRULE	COPPER OR BRASS ALLOY ROCKWELL F65 MAXIMUM	GOLD PLATE PER MIL-G-45204

COMPONENT	MATERIAL	FINISH
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCE ON FRAC. DEC. ANGLES ± 1/64 ±.005 ± 1°		
DRAWN BY TMCW DATE 10-18-82 CHECKED BY R.G. 10-20-82 APPROVED BY RMF 10/22/82		
AMP Incorporated 140 Fourth Avenue Waltham, MA 02451-7599		
TITLE OSM RIGHT ANGLE CABLE PLUG SOLDER ATTACHMENT M39012/56-3007 CAT A		
USE ASS'Y PROCEDURE 408-04931 NO. AP. (20-519)		
SIZE B CODE IDENT NO. 26805 2037-8007-92 REV 01 ₂		
SCALE 5:1 SHEET 1 OF 1		