


CONNETTORE TIPO A (CON MOLLA DI RITEGNO ESTERNA)
CONNECTOR TYPE A (WITH EXTERNAL SPRING)






ROSSO (RED)	---				
GIALLO (YELLOW)	---				
MARRONE (BROWN)	---				
BLU (BLUE)	---	3	////	ACCIAIO INOX (STAINLESS STEEL)	MOLLA (SPRING)
VERDE (GREEN)	---	2	NATURALE (NATURAL)	GOMMA (RUBBER)	GUARNIZIONE (RUBBER GASKET)
NATURALE (NATUR)	---	1	////	PA 6.6	BLOCCETTO (HOUSING)
GRIGIO (GREY)	282194-2				
NERO (BLACK)	282194-1				
COLORE COLOR	NUMERO PART. N°	N° (ITEM)	FINITURA / COLORE (FINISH / COLOUR)	MATERIALE (MATERIAL)	DESCRIZIONE (DESCRIPTION)
M	ECR-14-003472	MP	24MAR 2014	CUSTOMER DWG. FOR REFERENCE ONLY	
L	AGGIOR. CON ET00-0221-96 REVISED FOR ET00-0221-96	A.F.	27-5 '96	DISEGNO PER CLIENTE SOLO PER RIFERIMENTO	
H	AGGIOR. CON ET00-0108-95 REVISED FOR ET00-0108-95	M.P.	11-5 '95	THIS DRAWING IS UNPUBLISHED RELEASE FOR PUBLICATION	
G	AGG. FOGLIO 2 (ADDED SH.2)	R.M.	3-8 92	© COPYRIGHT 1996 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHT RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENT AND/OR PATENT PENDING	
F	IN PRODUZIONE (IN PRODUCTION)	R.M.	13-10 92	TOLLERANZE: SE NON DIVERSAMENTE SPECIFICATO	
E	AGGIORNATO (REVISED)	R.M.	26-5 92	TOLLERANZE, UNLESS OTHERWISE SPECIFIED	
D	AGGIORNATO (REVISED)	R.M.	17-3 92	DIAM. ISOLANTE (INS. DIA. RANGE)	
C	AGGIORNATO (REVISED)	R.M.	2-3 92	RANGO FILO (WIRE RANGE)	
B	AGGIORNATO (REVISED)	R.M.	4-9 91	SCALA (SCALE)	
A	WAS P/N C-90-51265-70	C.E.	2.91	1.5-3.0 (REDUCED INS. CABLE)	
REV.	REVISIONI (REVISION RECORD)	DIS. DATA (DR)	DATE	ANGOLI (ANGLES)	
				± 0.3	
				± 2°	
				DIS. NOV. 9. '90 (DR.)	
				Ennio CINI	
				CONT. 13 OCT 92 (CHK)	
				C. TARTARI	
				DESCRIZIONE (DESCRIPTION)	
				7 W. SPLASH PROOF CONN. ASS'Y with SECONDARY LOCK	
				LOC. SIZE NUMERO (DWG NO)	
				I A3 C-282194	
				REV. FOGLIO (SHEET)	
				M 1	
				DI (CF) 2	

DISTRIBUZIONE
(PRINT DIST.)

SCALA NON IMPEGNATIVA
(DO NOT SCALE)
DIMENSIONI IN mm
(DIMENSIONS IN)

METRIC

PROIEZIONE EUROPEA
(EUROPEAN PROJECTION)



DETT. LINGUETTA TAB-SCALA 5:1-
(TAB DETAIL)

FORMA ALTERNATIVA PERMESSA CON RAGGIO
(ALLOWED ALTERNATIVE PROFILE RADIUS)

VISTA DA "B"
VIEW FROM "B"

- 1 QUOTE APPLICABILI PER SFORMATURA PEZZO
(DRAFT PERMITTED TO FACILITATE REMOVAL OF PART FROM THE MOULD)
- 2 MATERIALE LINGUETTE: LEGA DI RAME STAGNATA, ES. OTTONE STAGNATO.
(TAB CONTACT MATERIAL: TIN PLATED COPPER ALLOY, E.G. BRASS TIN PLATED)
- 3 MATERIALE BLOCCHETTO: TERMOPLASTICO CARICATO FIBRA VETRO.
(HOUSING MATERIAL: THERMOPLASTIC, GLASS FIBER FILLED)

DISTRIBUZIONE
(PRINT DIST.)

FINITURA / COLORE (FINISH / COLOUR)		MATERIALE (MATERIAL)		NUMERO (PART NUMBER)	
CUSTOMER DWG. FOR REFERENCE ONLY		DISEGNO PER CLIENTE SOLO PER RIFERIMENTO		19	
THIS DRAWING IS UNPUBLISHED		RELEASE FOR PUBLICATION		19	
© COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHT RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENT AND/OR PATENT PENDING		TOLLERANZE, SE NON DIVERSAMENTE SPECIFICATO (TOLERANCES, UNLESS OTHERWISE SPECIFIED)		DIAM. ISOLANTE (INS. DIA. RANGE)	
± 0.3		ANGOLI (ANGLES)		RANGO FILO (WIRE RANGE)	
± 2°		DIS. (DR.)		SCALA (SCALE)	
CONT. (CHK)		DESCRIZIONE (DESCRIPTION)		7 POS. SPLASH PROOF CONN. ASS'Y with SECONDARY LOCK	
LOC. SIZE		NUMERO (DWG NO)		REV.	
I A3		C-282194		- 2	
REV. (REV. DATE)		DIS. DATA (DR. DATE)		Foglio (SHEET)	
SEE SHEET 1 OF 2		APP. (APP. DATE)		D1 (OF) 2	