





REV.	DATE	DESCRIPTION
NC	12/09/03	INITIAL RELEASE



RECOMMENDED CABLE
STRIPPING DIMS.



CRIMP NOTES:

1. CRIMPED FERRULE
HEX CRIMP SIZE .213"
2. CONTACT PIN TO SOLDER

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS	DATE	Amphenol Connex									
8						DRAWN	G.R.S.						12/09/03				
7						CHECKED											
6						ISSUED			PART DESCRIPTION SMC CRIMP PLUG (FOR RG-58/U CABLE)								
5						SHEET	1 OF 1							PART NO. 152134			
4	FERRULE	COPPER	GOLD	1	CAD FILE C:/152/152134.DWG			DWG. NO.		152134.DWG	REV.	NC	SIZE				
3	CONTACT PIN	BER. COPPER	GOLD	1													
2	INSULATOR	TEFLON	NATURAL	1													
1	BODY	BRASS	GOLD	1													
	DESCRIPTION	MATERIAL	FINISH	QTY													