

Slim Line Compact keyboard G84-4100



Key benefits

Cherry ML technology
with Gold Crosspoint contacts

Small measurements

Light weight

With or without Windows™ keys

Technical data

Interface

USB

PS/2 via adapter (included in delivery)

Current input

USB: max. 100 mA

PS/2: max. 50 mA

Number of keys

86 = with Windows™ keys

83 = without Windows™ keys

Operating life of individual keys

> 50 million operations

Cable length

approx. 1.75 m

Weight

approx. 398 g (without packaging)

approx. 510 g (with packaging)

Approvals

CE, VDE/ÜG (EN60950), cURus,
FCC DoC Cl. B, VCCI Cl. 2, BSMI, C-Tick

System requirements

USB or PS/2 connection

Delivery volume

Keyboard, Manual

Dimensions

approx. 282 x 132 x 27 mm (keyboard)

approx. 285 x 135 x 30 mm (packaging)

Reliability

MCBF > 10⁹ operations

MTBF > 90 000 hours

Storage temperature

-25 °C to 65 °C

Operating temperature

0 °C to 50 °C

Packaging Unit

42 keyboards per master carton

336 keyboards per pallet

Guarantee period

2 years

Order description

Order number	Number of keys	Colour	Connection
G84-4100LCMxx-0	86	light grey	Combo (USB . PS/2)
G84-4100PTMxx	86	black	Combo (USB . PS/2)
G84-4100LCAxx-0	83	light grey	Combo (USB . PS/2)
G84-4100PTAxx	83	black	Combo (USB . PS/2)

The xx in the order number defines the country version.

BE Belgium
CH Switzerland
DE Germany
DK Denmark
ES Spanish
EU US English/ international with €
FR France
GB English (UK)
IT Ital.
NO Norway
PO Portugal
SF Sweden/Finland
US US-English

Other country versions upon request.

Cherry GmbH
Cherrystraße
D-91275 Auerbach/Opf.
Telefon: +49 9643 18-0
Hotline: +49 9643 18-206
Fax: +49 9643 18-1545
Internet: www.cherrycorp.com
www.cherry.de

The manufacturer accepts no liability for errors or non-availability, and reserves the right to change specifications without prior notice.
Technical data relate to product specifications only.
Features may differ from those described. Only drawings combined with product specifications shall be deemed binding.

© 2004 Cherry GmbH