







- 1 HOUSING: NYLON OR POLYESTER, FLAME RETARDANT, UL 94V-0 RATED, GLASS FILLED, BLACK.
CONTACTS: PHOSPHOR BRONZE.
SHELL: CARBON STEEL
EYELETS: BRASS
INSERTS: ZINC
BOARDLOCKS: COPPER ALLOY
- 2 SHELL: .000100 MIN TIN OVER .000050 MIN COPPER.
CONTACTS: .000030 GOLD MIN FOR A DISTANCE OF .100 MIN FROM MATING END,
.000100 MIN TIN ON TERMINATION END, ALL OVER .000050 MIN NICKEL
ON ENTIRE CONTACT.
EYELETS: .000050 MIN TIN OVER COPPER FLASH.
BOARDLOCKS: .000150 MIN TIN OVER .000050 MIN NICKEL.
INSERTS: CLEAR CHROMATE

COPYRIGHT 2005
TYCO ELECTRONICS CORP
ALL RIGHTS RESERVED

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN G. ATTADIA - 04-12-05 CHK S. BOLASH 04-12-05 APVD M. WALMSLEY 04-12-05	Tyco Electronics Corporation Harrisburg, PA 17105-3608
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC 108-40025 APPLICATION SPEC 114-40010	NAME RECEPTACLE ASSEMBLY, SIZE 4, 37 POSITION, RIGHT ANGLE, FRONT METAL SHELL, .590 SERIES, .026 DIA POSTS, BOARDLOCKS, AMPLIMITE HD-20
MATERIAL	FINISH	WEIGHT -	SIZE A1
1	2	CUSTOMER DRAWING	SCALE 4:1 SHEET 1 OF 1 REV Q