



Application Range

In areas where mechanical and chemical stability are critical. For use on measurement and control technology and machine manufacturing.

Technical Data

Material:	Body:	Nickel Plated Brass
	Insert:	Polyamide
	Seal:	CR/NBR
	O Ring:	NBR

Protection Rating: IP68 – 5 bar

Temperature Range: -30°C to +100°C

Article List

Part Number	Description	Thread Size	Clamping Range (mm)	Spanner Wrench (mm)	Overall Length (mm)	Thread Length (mm)
390088	Brass Cable Gland	PG7	2 – 6.5	14	25	5
390094	Brass Cable Gland	PG9	4 - 8	17	29	6
390101	Brass Cable Gland	PG11	4 - 10	20	32	6
390123	Brass Cable Gland	PG16	8 - 14	24	35	6.5
2127668	Brass Cable Gland	PG21	11 - 18	30	40	7
2127674	Brass Cable Gland	PG29	16 - 25	40	48	8
2127680	Brass Cable Gland	PG36	19 - 32	50	62	15
2438851	Brass Cable Gland, Reduced Insert	PG7	2 – 5	14	25	5
2438867	Brass Cable Gland, Reduced Insert	PG9	2 – 6	17	29	6

Part Number	Description	Thread Size	Clamping Range (mm)	Spanner Wrench (mm)	Overall Length (mm)	Thread Length (mm)
2438873	Brass Cable Gland, Reduced Insert	PG11	3 - 7	20	32	6
2438889	Brass Cable Gland, Reduced Insert	PG13.5	4 - 9	22	34	6.5
2438895	Brass Cable Gland, Reduced Insert	PG16	6 - 13	24	35	6.5
2438902	Brass Cable Gland, Reduced Insert	PG21	8 - 16	30	40	7
2439674	Brass Cable Gland, Reduced Insert	PG29	10.5 - 20	40	48	8
2438918	Brass Cable Gland, Reduced Insert	PG36	19 -26	50	62	15
4058817	Brass Cable Gland	M12	3 – 7	16	26.5	6.5
4058823	Brass Cable Gland	M16	4.5 – 10	20	32	7
4058839	Brass Cable Gland	M20	7 – 13	24	35.5	8
4058845	Brass Cable Gland	M25	9 – 17	29	37.5	8
4058851	Brass Cable Gland	M32	11 – 21	36	42.2	9
4058867	Brass Cable Gland	M40	19 – 28	45	49.5	9
4058889	Brass Cable Gland	M50	27 – 35	54	52	10
4058895	Brass Cable Gland	M63	34 – 45	67	61.3	15