




- △ HOUSING: POLYESTER, UL 94V-0 RATED, BLACK.
CONTACT: PHOSPHOR BRONZE.
SCREWLOCK: BRASS.
SHELL: CARBON STEEL.
- △ SHELL: 5.08um [0.000200] MIN TIN OVER 2.54um [0.000100] MIN COPPER.
CONTACT: 0.76um [0.000030] MIN GOLD FOR A LENGTH OF 1.40 [0.055] MIN FROM MATING END, 2.54um [0.000100] MIN TIN OR TIN-LEAD ON OPPOSITE END, BOTH OVER 0.76um [0.000030] MIN NICKEL.
SCREWLOCK: 2.54um [0.000100] MIN TIN-LEAD OVER 1.27um [0.000050] MIN NICKEL OVER COPPER FLASH.
3. NOTE DELETED.
- △ DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.
- △ 2.79[.110] MAX IN SHELL TAB CLINCH AREAS.
- △ ORIENTATION IS OPTIONAL AND MAY NOT BE AS SHOWN.