

RoHS




KF22X Series

Right Angle PCB Mount .318" Footprint with Ferrite

KF22X Series Dimensions

Pictured with Board Lock Option, Dimensions in mm



Shell Size In mm	A ±.010 ±0.25	A1 ±.010 ±0.25	B ±.005 ±0.13	C ±.015 ±0.38
9 (E)	.643 16.33	.666 16.92	.984 24.99	1.213 30.81
15 (A)	.971 24.66	.994 25.25	1.312 33.32	1.541 39.14
25 (B)	1.511 38.38	1.534 38.96	1.852 47.04	2.088 53.04
37 (C)	2.159 54.84	2.182 55.42	2.500 63.50	2.729 69.32

A = Exterior of Female Shell (S) A1 = Interior of Male Shell (P)

FERRITE D-SUBMINIATURE

KF22X Series

Documentation & Ordering Information

Kycon Part

Part Number Builder

Series	Shell Size	Contact Type	PCB Mounting Options	Front Panel Mounting Options	Plating Option
--------	------------	--------------	----------------------	------------------------------	----------------

Series

KF22X - D-Subminiature Connector, .318" Footprint with Ferrite

Shell Size-Contact Option

E - 9 Contacts

A - 15 Contacts

B - 25 Contacts

C - 37 Contacts



Contact Type

P - Pin Contact (Plug)

S - Socket Contact (Receptacle)

PC Board Mounting Option

N Option



Front Panel Mounting Option


Standard

J Option




R Option

T Option

JM Option



4-40 Jack Screws Installed



M3 Jack Screws Installed

Plating Option

Blank - Gold Flash

15 - 15µ" Gold

30 - 30µ" Gold

Contact Kycon for other options