




Heyco-Flex™ V Nylon Slit Tubing

- Slit design allows side entry and encirclement of preassembled harnesses and capillary tubes.
- Unique slit design allows for wire breakouts.
- Heyco-Flex V is lightweight and flexible, yet durable enough to meet your wire management requirements.
- Multiple sizes 1/8" to 1-1/2".
- All nylon construction resists salt water, weak acids, gasoline, alcohol, oil, grease, and common solvents.
- Quick installation; cuts with utility knife, PVC cutter or Heyco cutting tool #8340. See page 2-4.

NOMINAL DIAMETER	PART NO. Black	DESCRIPTION	PART DIMENSIONS						ROLL LENGTH
			A Outside Diameter		B Inside Diameter		Wall Thickness Range		
in.			in.	mm.	in	mm.	in.	mm.	ft.
1/8	1634A	HF5 1/8	.260	6,6	.168	4,3	.007-.019	0,18-0,48	100
1/4	1635A	HF5 1/4	.390	9,9	.288	7,3			
11/32	1636A	HF5 11/32	.511	13,0	.345	8,8			
3/8	1637A	HF5 3/8	.532	13,5	.415	10,5			
7/16	1638A	HF5 7/16	.625	15,9	.442	11,2	.007-.019	0,18-0,48	100
1/2	1639A	HF5 1/2	.635	16,2	.525	13,3			
5/8	1641A	HF5 5/8	.806	20,5	.663	16,8			
3/4	1642A	HF5 3/4	.928	23,6	.790	20,1			
1	1643A	HF5 1	1.122	28,5	.917	23,3	.007-.019	0,18-0,48	100
1-1/16	1644A	HF5 1-1/16	1.215	30,9	1.010	25,6			
1-1/4	1646A	HF5 1-1/4	1.492	37,9	1.283	32,6			
1-1/2	1649A	HF5 1-1/2	1.734	43,9	1.465	37,2			

Standard color black.



*Quick
Specs*

Material
Temperature Range of Use
Flammability Rating

Polyamide 6 Nylon
-40°C to 115°C (-40°F to 239°F) Continuous
-40°C to 190°C (-40°F to 374°F) Intermittent
94HB

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Heyco:](#)

[9032](#) [9062](#) [1642A](#) [1634A](#) [1644A](#)