


ED705/X (5.0 mm) EDZ705/X (5.08 mm)



2-12 poles, Spacing 5.0 mm and 5.08 mm
insert required no. of poles **x**
How to order see page 5



Ratings:

Rated Voltage	300 V	250 V
Rated Current	15 A	24 A (T60)
Wire Size	AWG 22-14	2.5 mm ²
Test Voltage		2.0 kV
Rated Torque/ScrewSize		0.5 Nm/M3

Max. Rated Cross Section

Single Wire (solid)	4.0 mm ²
Stranded Wire (flexible)	2.5 mm ²
Stranded wire with Ferrules	2.5 mm ²

Dimensions

Spacing	5.0 mm (5.08 mm)
PCB Hole Diameter	1.3 mm
Stripped Length	8.0 mm

Materials

Insulating Material	PA
Flammability Class	UL94 V-0
Temperature Range	-30°C/+105°C
Terminal Block	CuZn
Wire Guard	Cu

Color

Green

