


EDSTL1550/X (3.5 mm) EDSTLZ1550/X (3.81 mm)



2-20 (16) poles, Spacing 3.5 mm or 3.81 mm
insert required no. of poles **X**
How to order see page 5



Ratings:

Rated Voltage	300 V	160 V
Rated Current	8 A	9 A (T60)
Rating Impulse Voltage/Dirt Level		4 kV/3

Dimensions

Spacing	3.5 mm (3.81 mm)
PCB Hole Diameter	1.2 mm

Materials

Insulating Material	PA
Flammability Class	UL94 V-0
Temperature Range	-30°C/+105°C
Contact Pin	Cu

Color

Green

