





- CONTACTS QUALIFIED TO GSFC-S-311-P-4/10, NASA P/N G-10-S1
- ALL DIAMETERS ARE CONCENTRIC WITH EACH OTHER WITHIN .004 T.I.R.
- ALL SURFACES HAVE $\sqrt[63]{}$ OR BETTER FINISH.
- POINT OF PLATING THICKNESS MEASUREMENT.
- SLEEVE MAY BE CRIMPED OR DIMPLED TO BODY.
- ~~MINIMUM SEPERATION FORCE OF 7 OZ USING A .039 PIN AND 4 OZ MAX ENGAGEMENT FORCE USING A .041 PIN.~~
- OPTIONAL LOCATION FOR STAMPED LETTER "A"
- PLATING: GOLD PER ASTM-B-488 (TYPEII) OVER COPPER PER MIL-C-14550, CLASS 4.
- PLATING: GOLD PER ASTM-B-488 (TYPEII) OVER NICKEL PER AMS-QQ-N-290.
- CONTACTS MEET REQUIREMENTS OF AS39029/63-368
- RESTRICTED PART NUMBER.



TAPE MOUNTED
PART NO 206793-2 ONLY
SCALE 2:1

11			1-206793-1
	9	AS SHOWN	206793-4
OBSOLETE	8	SAME AS -1 EXCEPT 6	206793-3
1	8	SAME AS -1 EXCEPT TAPE MOUNTED 5,000 CONTACTS PER REEL	206793-2
1	8	AS SHOWN	206793-1
	FINISH	DESCRIPTION	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C.THOMAS 11-20-02	TE TE Connectivity								
DIMENSIONS: INCHES		CHK D.MILLER 11-20-02									
		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME SOCKET CONTACT ASSY, SIZE 20, AMPLIMITE							
		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± - FINISH -		APVD D.MILLER 11-20-02		DRAWING NO					
MATERIAL SEE CALLOUT		PRODUCT SPEC		APPLICATION SPEC		SIZE CAGE CODE		DRAWING NO		RESTRICTED TO	
		WEIGHT 0.000000		A2 00779		C=206793					
		CUSTOMER DRAWING		SCALE 20:1		SHEET 1 of 1		REV L			