




REV. D
DCO 301385

TOLERANCES $\pm .010"$ - UNLESS
OTHERWISE SPECIFIED

COIL: @ 25°C

RESISTANCE	500 OHMS $\pm 10\%$
NOMINAL VOLTAGE	28 VDC
MUST OPERATE	13.5 VDC MAX.
TRANSIENT SUPPRESSION - 42 VDC MAX.	
MUST RELEASE	5.5 VDC MAX., 2.3 VDC MIN.

ENVIRONMENT:

10	55	$.06"$ DA
55	500	10 g's
VIBRATION	500 Hz TO 3000 Hz	@ 20 g's
SHOCK	50 g's	11 MS. DURATION
TEMPERATURE	-70 $^{\circ}\text{C}$ TO +125 $^{\circ}\text{C}$	


NOTES: OPERATE, RELEASE 5 MS MAX.

CONTACT STABILIZATION 2.5 MS MAX.

CONTACT BOUNCE 1 MS MAX.

CONTACT BREAK BOUNCE 0.1 MS MAX.

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: LOW LEVEL
TO 5 AMPS 28 VDC, 115 VAC 400 Hz RESISTIVE,
100,000 OPERATIONS

DR. R.F. 25APR2011 CK. M.B. 26APR2011



CUST. QPL
CUST. NO. M83536/2-028M REV.

TE NUMBER
5-1617758-4

CII PART NUMBER
FCB-205-0228M