


Search within category

GO

BUY NOW

DESIGN / INSTALL



UTP28CH4BU

Category 5e performance, 28 AWG UTP patch cord with Pan-Plug™ Modular Plugs on each end. Blue. 4 ft.

Specs

Packaging Details

Documents

★ Add to Favorites

Add to BOM

Conductor Gauge (AWG)	28
Performance Level	Category 5e
Overall Length (ft.)	4
Overall Length (m)	1.2
Maximum Operating Temperature (°C)	75
Maximum Operating Temperature (°F)	167
Minimum Operating Temperature (°C)	-10
Minimum Operating Temperature (°F)	14
Maximum Storage Temperature (°C)	70
Maximum Storage Temperature (°F)	158
Minimum Storage Temperature (°C)	-40
Minimum Storage Temperature (°F)	-40
Flammability Rating	CM, LSZH-1 (60332-1)
Standards Met	IEEE 802.3af, 802.3at, 802.3bt type 3 and type 4, UL 1863.
Cable Color	Blue
Length (ft.)	4.00
Termination End 1	Modular Plug
Termination End 2	Modular Plug
CE Compliant	Yes
Nominal Cable Outside Diameter (In.)	0.15
Nominal Cable Outside Diameter (mm)	3.8
UL5A Listed	No
Boot Color	No Boot
Cable Length (ft.)	28.00
Cable Type	U/UTP
Conductor Material	Copper
Maximum Installation Temperature (°C)	70

Maximum Installation Temperature (°F)	158
Minimum Installation Temperature (°C)	70
Minimum Installation Temperature (°F)	-40
Part Features	100% performance tested for wire map, NEXT and return loss, Centered de-embedded plug, Integral pair manager, Patented tangle-free latch
RoHS Compliancy Status	Compliant
Min. Order Qty.	1
