

CATALOG

➔ Cross Reference

[Competitive](#)[Products](#)[Military Spec P/Ns](#)[Tyco Brand P/Ns](#)➔ [Part Number Search](#)➔ [Document Search](#)➔ [Product Type Search](#)➔ [Product Family Search](#)➔ [Alphabetical Search](#)➔ [RoHS/ELV Compliance &
Alternates](#)➔ [CAD Model Search](#)➔ [Brand Search](#)➔ [Tool Search](#)➔ [Multiple Part Comparison](#)➔ [Lead Free Solutions](#)➔ [Help/Glossary](#)[Home](#)

e-bulletin newsletter


SUBSCRIBE NOW!
click here

Sockets

➔ SIP Sockets

**2-1437535-9 (510-AG91D-10)**  ActiveNot ELV or RoHS Compliant**(Corporate P/N: 2-1437535-9)**[Search for Compliant](#)[\(RoHS/ELV\) Alternates](#)[Search for Parts](#)

Document links for this part cannot be displayed. Your browser does not support inline frames or is currently configured not to display inline frames. Inline frames are supported in both Internet Explorer 5 and Netscape 6, as well as all later versions of these browsers.

Related Part Information

General Information	eCommerce	Related Part Information
➤ General Info ➤ Sales Info ➤ Assembly Subcontractors	➤ Pricing ➤ Product Availability	➤ Tooling

Searchable Features:

Brand:	AMP
RoHS/ELV Compliance:	Not ELV/RoHS compliant
Lead Free Solder Processes:	Wave solder capable to 240° C, Wave solder capable to 265° C
Number of Positions:	10
Contact Style:	Screw Machine
Leg Style:	Standard
Contact Material:	Beryllium Copper
Contact Mating Area Plating:	Gold (30)

Other Properties:

Sleeve Plating:	Tin-Lead
Housing Material:	Thermoplastic Polyester
Housing Flammability Rating:	UL 94V-0
Breakaway Header:	Yes

Termination Post Length (mm [in]):	3.18 [0.125]
Sleeve Material:	Brass

[Copyright](#) and [Privacy Statement](#)
Visit [Tyco International Ltd.](#)

[[Products](#) | [Catalog](#) | [Brands](#) | [Industries](#) | [Commerce](#) | [Supplier](#) | [Contact Us](#) | [About](#) | [Home](#)]