






- ③ TWO .000030 MIN THK. GOLD STRIPES IN CONTACT AREA WITH TIN-LEAD (93/7) ON CONTACT LEGS, BALANCE OF CONTACT NICKEL PLATED.
- ④ TWO .000015 MIN THK. GOLD STRIPES IN CONTACT AREA WITH TIN-LEAD (93/7) ON CONTACT LEGS, BALANCE OF CONTACT NICKEL PLATED.
- ⑤ MAXIMUM DIMENSION FOR I.C. SEATING PLANE.



SUPSD BY 390261-3		△	PHOS.BRZ. .006 THK	GLASS-FILLED THERMOPLASTIC, 94V-0, BLACK	2-640357-4
OBSOLETE		TINNED	PHOS.BRZ. .006 THK	GLASS-FILLED THERMOPLASTIC, 94V-0, BLACK	2-640357-3
SUPSD BY 390261-3		△	BE.CU. .006 THK	GLASS-FILLED THERMOPLASTIC, 94V-0, BLACK	2-640357-2
		TINNED	BE.CU. .006 THK	GLASS-FILLED THERMOPLASTIC, 94V-0, BLACK	2-640357-1
CONTACT FINISH			CONTACT MAT'L	HOUSING MATERIAL	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DATE 20 FEB 87	TYPED BY M.CYRUS		TYPED BY Tycos Electronics Corporation Harrisburg, PA 17105	
DRAWN BY R.MILLER		20 FEB 87	CHECKED BY J.LAMBERT		NAME	
DIMENSIONS: INCHES		TO DIMENSIONS UNLESS OTHERWISE SPECIFIED		PRODUCT SPEC 108-1066		SOCKET ASSY, DIP, 14 POS, DIPLOMATE DL -
		0 PLG ± - 1 PLG ± - 2 PLG ± - 3 PLG ± .005 4 PLG ± - ANGLES ± -		APPLICATION SPEC 114-1049		
MATERIAL SEE TABLE		FINISH SEE TABLE		WEIGHT -		
				SIZE A1	CAGE CODE 00779	DRAWING NO C-640357
				RESTRICTED TO -		
				CUSTOMER DRAWING		
				SCALE 5:1	SHEET 1 of 1	REV Z