


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO.*	BUNDLE DIA.		A	B	C	D	E	F	G	H	MIN. LOOP TENSILE lbs. (N)	CROSS- SECTION	RECM. FAST.	WEIGHT lbs./100pcs. (g)
	MIN. in. (mm)	MAX. in. (mm)	in. (mm)	in. (mm)	in. (mm)	in. (mm)	in. (mm)	in. (mm)	in. (mm)					
SSC2S-S10	.06 (1.5)	1.75 (44)	.045 (1.1)	.180 (4.6)	.310 (7.9)	.772 (19.6)	.430 (10.9)	7.35 (187)	.200 (5.1)	.075 (1.9)	50 (222)	STANDARD	#10 (M5) SCREW	.3 (136)
SSC2S-S6	.06 (1.5)	1.75 (44)	.045 (1.1)	.180 (4.6)	.310 (7.9)	.772 (19.6)	.430 (10.9)	7.35 (187)	.148 (3.8)	.075 (1.9)	50 (222)	STANDARD	#6 (M3) SCREW	.3 (136)
SSC4S-S10	.06 (1.5)	4.00 (102)	.045 (1.1)	.180 (4.6)	.310 (7.9)	.772 (19.6)	.400 (10.2)	15.67 (398)	.200 (5.1)	.075 (1.9)	50 (222)	STANDARD	#10 (M5) SCREW	.5 (227)
SSC4H-S25	.06 (1.5)	4.00 (102)	.065 (1.7)	.300 (7.6)	.460 (11.7)	.930 (23.6)	.530 (13.5)	15.55 (395)	.260 (6.6)	.110 (2.8)	120 (534)	HEAVY	1/4 (M6) SCREW	1.3 (590)

NOTES:

- *1) SEE www.panduit.com FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE, PART MATERIAL AND PART COLOR.
2) RECOGNIZED UNDER THE COMPONENT PROGRAM OF UNDERWRITERS LABORATORIES INC.

W10001EB/21-SS-600

										DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS.		
										PANDUIT CORP. TINLEY PARK, ILLINOIS		
										STA-STRAP CLAMP CABLE TIES SSC SERIES		
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .005 (.XXX) ± .020(.51) (.XX) ± .02(.5) ANGLES ± .005		
										UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.		
---	----	---		CHG NOTE 1, "SEE CURRENT PRICE..." TO "SEE www.panduit.com..."		----	---			DRAWN BY JABO	MAT'L:	
21	2/15/11	JABO	TGS	REMOVED PART, SEE ECN FOR DETAILS		SS-600	21	TGS		DATE 1/8/02	NYLON 6.6	
REV	DATE	BY	CHK	DESCRIPTION		ECN - R		CUST	SUP	CHK'D JVL		DRAWING NO. SS-600