

**Connection cable for 25-pin ports
serial / parallel**

AK 401 2 m
AK 508 3 m DSUB 25-pin, Male <=> DSUB 25-pin, Male
AK 402 5 m
AK 403 7 m snap-in hoods

cable 25-wire, single shielded, configuration 1:1



**Connection cable for 25-pin ports
serial / parallel**

AK 404 2 m
AK 526 3 m DSUB 25-pin, Male <=> DSUB 25-pin, Female
AK 405 5 m
AK 406 7 m speedy hoods

cable 25-wire, shielded, configuration 1:1



**Connection cable for 25-pin ports
serial / parallel**

AK 407 2 m DSUB 25-pin, Female <=> DSUB 25-pin, Female

snap-in hoods

cable 25-wire, single shielded, configuration 1:1




Extension cable for Centronics connection

AK 410 2 m CENT 36-pin, Male <=> CENT 36-pin, Male

metall hoods

cable 36-wire, single shielded, configuration 1:1



**High-Quality extension cable
for Centronics connection**

AK 425 1 m
AK 138 2 m CENT 36-pin, Male <=> CENT 36-pin, Male
AK 426 3 m
AK 139 5 m
AK 427 7 m molded hoods

cable 36-wire, single shielded, configuration 1:1



High-Quality interface extension cable

AK 135 2 m DSUB 25-pin, Male <=> DSUB 25-pin, Female
AK 166 3 m
AK 136 5 m
AK 168 10 m molded hoods

cable 25-wire, single shielded, configuration 1:1



High-Quality interface extension cable

AK 137 2 m DSUB 25-pin, Male <=> DSUB 25-pin, Male
AK 162 3 m
AK 154 5 m
AK 163 7 m
AK 164 10 m molded hoods

cable 25-wire, single shielded, configuration 1:1



AK 419 2 m

IEEE 488-Bus, special cable

CENT 24-pin, Male/Female <=>
CENT 24-pin, Male/Female

Metallized plastic hoods with knurled screws

UL2464, Twisted Pair, double shielded



WWW.USA-ASSMANN.COM

TEL: 1-877-ASSMANN

FAX: 1-602-897-7255