


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

RoHS Compliant ✓


REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	CN RELEASE	2/25/08	D.GRIFFIN
B	ECN 4474; ADDED 1.0 FT LENGTH, UPDATED FORMAT, CHG'D NOTES, RoHS	1/7/10	D. CASTRO



WIRING MAP						
"P1"	COLOR	"P2"		"P1"	COLOR	"P2"
1	BLACK	1		14	BROWN/WHITE	14
2	BROWN	2		15	RED/WHITE	15
3	RED	3		16	ORANGE/WHITE	16
4	ORANGE	4		17	GREEN/WHITE	17
5	YELLOW	5		18	BLUE/WHITE	18
6	GREEN	6		19	PURPLE/WHITE	19
7	BLUE	7		20	RED/BLACK	20
8	PURPLE	8		21	ORANGE/BLACK	21
9	GRAY	9		22	YELLOW/BLACK	22
10	WHITE	10		23	GREEN/BLACK	23
11	PINK	11		24	GRAY/BLACK	24
12	LIGHT GREEN	12		25	PINK/BLACK	25
13	BLACK/WHITE	13		SHELL	DRAIN WIRE	SHELL

PART NUMBER	LENGTH	
	FEET	METERS
CSMNB25MM-1	1.0	0.31
CSMNB25MM-2.5	2.5	0.76
CSMNB25MM-5	5.0	1.52
CSMNB25MM-10	10.0	3.05
CSMNB25MM-15	15.0	4.57
CSMNB25MM-25	25.0	7.62
CSMNB25MM-50	50.0	15.24

- NOTES:**
- CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
 - CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM PACKAGING SPEC. PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	DRAWN BY D.FRISIELLO	2/22/08		
	CHECKED BY D.FORTIN	2/22/08	CATEGORY D-SUBMINIATURE	
	APPROVED BY S.SMITH	2/22/08	PRODUCT DESCRIPTION CABLE, DB25M/M MOLDED BLK	
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		SIZE A	FSCM NO. 43321
COLOR VARIATIONS MAY OCCUR		DWG. NO. CSMNB25MM	REV. B	SCALE: NONE
		CAD FILE: CSMNB25MM.SLDDRW	SHEET 1 OF 1	