

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

15266-0265

Status:

Active

Overview:

Premo-Flex™ FFC and Etched Polyimide Jumpers

Description:

0.50mm Pitch Premo-Flex™ FFC Jumper, Same Side Contacts (Type A), 24 Circuits, 0.229m Cable Length, 0.27mm Cable Thickness, Tin (Sn) Plating



Series

image - Reference only

Documents:

- Drawing (PDF)

Product Specification PS-15266-001 (PDF)
- Packaging Specification PK-15266-001 (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family	Cable
Series	15266
Comments	Contacts on the same side, Type A
Crimp Quality Equipment	Yes
Overview	Premo-Flex™ FFC and Etched Polyimide Jumpers
Product Name	Premo-Flex™ FFC Jumper
UPC	884982434714

Physical

Cable Length	0.229m
Circuits (Loaded)	24
Circuits (maximum)	24
Net Weight	1.768/g
Packaging Type	Bag
Pitch - Termination Interface	0.50mm
Temperature Range - Operating	-40°C to +105°C
Wire Size AWG	N/A
Wire/Cable Type	Flat Flex Cable

Electrical

Current - Maximum per Contact	0.5A
Voltage - Maximum	60V AC

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-15266-001
Product Specification	PS-15266-001
Sales Drawing	SD-15266-001

EU RoHS

ELV and RoHS
Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product
environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

15266Series

Use With

Molex FFC – FPC connector.
Be sure to match like plating

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION