



APC Displays+
01480 226600
sales@apc-displays.co.uk

8.4" Open Frame

Part No : HE084AV
Item Description : 8.4" monitor / without touch

Advantage and Application

- long term availability of adopted TFT LCD panels (stability of supply for min. 3 years)
- Analog RGB / Video supportable
- Touch Screen (not adopted)
- RS232 communication (option)
- Fine finishing metal chassis (brilliant design & complete set level OSD button)
- Application
 - Kiosks
 - ATMs
 - Casino & Amusement games
 - Lottery and Ticket sales
 - Self-Services
 - Industrial process control

Item	Description
Frame / bezel Color	EGL in black
Display Type	Size: 8.4" diagonal, Type: Active matrix TFT LCD Aspect ratio: 4 x 3
Active area	170.4 (H) x 127.8 (V)
Optimal (native) resolution	800 x 600
Support color	16.2 M colors
Brightness (without touch)	450 cd/m2
Viewing Angles	80 / 80 / 80 / 60
Input video supportable	Analog RGB, Composite Video, Super Video
Temperature	Operating ; - 30°C ~ +85 °C Storage : - 30°C ~ +85 °C
Mounting Holes	VESA standard mounting 75 x 75 mm
Applicable Graphic Mode	VESA standard timing control
Weight & Volume	Unit Weight : 1,210 g Carton Packing : pcs Carton weight : Kg

