

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0010891047](#)
Status: **Obsolete**
Description: 2.54mm (.100") Pitch C-Grid® Breakaway Header, Low Profile, Dual Row, Right Angle, 4 Circuits, 8.13mm (.320") Mating Pin Length, 0.38µm (15µ") Gold (Au) Selective Plating

Documents:
[Drawing \(PDF\)](#)

Agency Certification
UL E29179

General
Product Family PCB Headers
Series [70203](#)
Application Board-to-Board, Signal, Wire-to-Board
Application Tooling Part Link 011201230
Product Name C-Grid®

Physical
Breakaway Yes
Circuits (Loaded) 4
Circuits (maximum) 4
Durability (mating cycles max) 50
Flammability 94V-0
Glow-Wire Compliant No
Lock to Mating Part None
Number of Rows 2
Orientation Right Angle
PC Tail Length 2.79mm (.110")
PCB Locator No
PCB Retention None
Packaging Type Tube
Pitch - Mating Interface 2.54mm (.100")
Polarized to Mating Part No
Polarized to PCB No
Shrouded No
Stackable Yes
Temperature Range - Operating -40°C to +105°C

Electrical
Current - Maximum per Contact 3A
Voltage - Maximum 250V

Solder Process Data
Lead-free Process Capability Wave Capable (TH only)

Material Info
Old Part Number 70203-0196




image - Reference only

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[70203Series](#)