



Fig. 1




BNC Panel Receptacles  
4 hole Square Flange, Rear or Front Mount  
**4500**  
**31-105**  
**31-203**  
**31-203-RFX**

Fig. 2



BNC Angle Bulkhead Receptacle  
**31-222**

Fig. 3



BNC Angle Panel Receptacle  
**5675**

## BNC PANEL AND ANGLE BULKHEAD RECEPTACLES

| Description                                                                    | Terminal Type | Dimensions, inches (millimeters) |            |            | Notes |      | Mtg. Hole | Military Number | Amphenol Number   | Fig. |
|--------------------------------------------------------------------------------|---------------|----------------------------------|------------|------------|-------|------|-----------|-----------------|-------------------|------|
|                                                                                |               | a                                | b          | c          | Plt.  | Ins. |           |                 |                   |      |
| Panel Receptacle 4 hole Square Flange<br>No. 3-56 Tapped Flange Holes          | Solder Cup    | 1.06(27.0)                       | .687(17.5) | .719(18.3) | P1    | D1   | L         | UG-290A/U       | <b>31-203</b>     | 1    |
| Panel Receptacle 4 hole Square Flange<br>.125" Dia. Flange Holes               | Solder Cup    | 1.06(27.0)                       | .687(17.5) | .719(18.3) | P7    | D23  | L         | —               | <b>31-203-RFX</b> |      |
| Panel Receptacle 4 hole Square Flange<br>.120" Dia. Flange Holes, Styrene Ins. | Solder Cup    | 1.03(26.2)                       | .687(17.5) | .719(18.3) | P1    | D6   | L         | —               | <b>31-105*</b>    |      |
| Panel Receptacle 4 hole Square Flange<br>.136" Dia. Flange Holes, Styrene Ins. | Turret        | 1.08(27.4)                       | .750(19.1) | .609(15.5) | P1    | D6   | N         | UG-185/U        | <b>4500*</b>      | 2    |
| Angle, External Tooth Lockwasher                                               | Solder Cup    | .906(23.0)                       | .594(15.1) | .625(15.8) | P1    | D1   | V         | UG-1098/U       | <b>31-222*</b> □  |      |
| Angle Panel Receptacle 4 hole Flange<br>.136"(3.5mm) Diameter Holes            | Solder Cup    | .928(23.6)                       | .642(16.3) | .642(16.3) | P1    | D1   | N         | UG-535/U        | <b>5675*</b>      |      |

\* recognized under the component program of U.L., Inc.

▲ distributor stocked

□ IBM 01620666